

'NEW' Pall RCA Series Deltadyne Differential Pressure Switch

Pall RCA series differential pressure indicators signal the need for filter element change by sensing the differential pressure between ports upstream and downstream of the filter element. They connect to the Deltadyne™ device port available on Pall filter housings.

Specifications

Fatigue Test Pressure:	1 Million cycles at 0-400 bar (5800psi)
Operating Temperature:	Maximum Fluid Operating Temperature 120 °C (250 °F) Minimum Operating Temperature -25 °C (-13 °F) Minimum Ambient Temperature -40 °C (-40 °F)
Fluid Compatibility:	Standard mineral oils and hydrocarbon-based synthetic Hydraulic and Lubrication fluids and Fuels
Materials of Construction:	Brass body
Seal Materials:	Fluorocarbon
Environmental:	IP67 to IEC 60529 connected or unconnected
Switch: <i>RCA216/217</i>	Normally closed single pole contacts open on differential pressure exceeding set point
Switching Voltage:	48V DC Maximum
Switching Current:	0.5 A Maximum
Electrical Connectors:	RCA 216 - Connector Deustch DT04-2P to mate with Deutsch DT06-2S receptacle RCA 217 - Connector AMP Junior timer to mate with AMP junior timer receptacle 827551-3 and contacts 925596-1
Switch: <i>RCA218M</i>	Single pole, double throw (SPDT) switch state changes on differential pressure exceeding set point
Switching Voltage:	48V DC Maximum or 250V AC
Switching Current:	4 A Maximum
Electrical Connectors:	Hirschmann type
Switch: <i>RCA218R</i>	Single pole, double throw (SPDT) switch state changes on differential pressure exceeding set point
Switching Voltage:	24V DC
Switching Current:	4 A Maximum
Electrical Connectors:	Hirschmann type with red and green LEDs that illuminate when switch operates
Visual indicator: <i>RCA219</i>	Window changes from white to red on detnation. All units automatically reset when differential pressure drops below set-point.
System Interface:	To fit all standard Pall threaded indicator ports



Pall RCA216 differential pressure switch



Pall RCA217 differential pressure switch



Pall RCA218M differential pressure indicator



Pall RCA218R differential pressure indicator



Pall RCA219 differential pressure indicator

Ordering Information

Differential Pressure Indicator P/N: RCA Z Z
Table 1 Table 2

Table 1 - Connector Option

Code	Connector
216C	Deutsch DT04-2P
217U	AMP Junior Timer
218M	Hirschmann
218R	Hirschmann with Red and Green LED indicators
219D	Visual Indicator


Table 2 - Pressure Setting

Code	Pressure
090	2.4 ± 0.3 bard (35 ± 4 psid)
091	3.4 ± 0.4 bard (50 ± 6 psid)

Other options available. Contact Pall Sales for information


Electrical Connection

216/217



The switch is wired normally closed. Using normally closed configuration allows for the detection of damaged or broken cables or disconnection. The switch will automatically reset when differential pressure is reduced.

218



Switch can be wired using either normally open or normally closed configuration. The switch will automatically reset when differential pressure is reduced.



25 Harbor Park Drive
 Port Washington NY 11050
 +1 516 484 3600 telephone
 +1 800 289 7255 toll free US

Portsmouth - UK
 +44 (0)23 9233 8000 telephone
 +44 (0)23 9233 8811 fax
 industrialeu@pall.com

Filtration. Separation. Solution.SM



Visit us on the Web at www.pall.com

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2014, Pall Corporation. Pall, Deltadyne and are trademarks of Pall Corporation.
 ® Indicates a trademark registered in the USA. Better Lives. Better Planet and **Filtration. Separation. Solution.SM** are service marks of Pall Corporation.